

# Eaton BR3060BQN150

Catalog Number: BR3060BQN150

BR loadcenter, 150A CSR MAIN BREAKER, 30 SPACES/60 CIRCUITS, 120/240V, ALUMINUM BUS, G1 INDOOR BOX SIZE, #2-300MCM INCOMING LUG SIZE, QUICK CONNECT NEUTRAL CONFIGURATION

## General specifications



Product Name	Eaton BR main breaker loadcenter	Catalog Number	BR3060BQN150
UPC	786676026277	Product Length/Depth	3.88 in
Product Height	34.13 in	Product Width	14.31 in
Product Weight	34 lb	Warranty	10 year

## Product specifications

### Special features

QUICK CONNECT NEUTRALS

### Type

Main circuit breaker

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

G1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR3060BQN150](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)