

Eaton BR3060BQN200R

Catalog Number: BR3060BQN200R

Quick connect neutrals, Main circuit breaker loadcenter, 200A, G1R, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 60 circuits, 30 spaces, Three-wire, Single-phase, #2 AWG-300 kcmil, Combination, Type BR 1-inch breakers, 120/240V

General specifications



Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR3060BQN200R
UPC	Product Length/Depth
786676026253	5.19 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
39 lb	10 year
Certifications	
UL Listed file E52977	

Product specifications

Special features

Quick connect neutrals

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

G1R

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR3060BQN200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)