

# Eaton BR3060LQN200RG

Catalog Number: BR3060LQN200RG

Eaton BR main lug loadcenter, 200 A,D1R,Aluminum, NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,60 Circuits,Twenty-four pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#1 AWG-300 kcmil Cu/Al

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR3060LQN200RG
<b>UPC</b>	<b>Product Length/Depth</b>
786676026321	5.19 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
35 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	GBK2120 installed

## Product specifications

### Type

Main lug

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Mounting

Combination

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

D1R

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

Eaton Specification Sheet - BR3060LQN200RG

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BR3060LQN200RG

Catalog Number: BR3060LQN200RG

Eaton BR main lug loadcenter, 200 A,D1R,Aluminum, NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,60 Circuits,Twenty-four pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#1 AWG-300 kcmil Cu/Al

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR3060LQN200RG
<b>UPC</b>	<b>Product Length/Depth</b>
786676026321	5.19 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
35 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	GBK2120 installed

## Product specifications

### Type

Main lug

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Mounting

Combination

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

D1R

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

Eaton Specification Sheet - BR3060LQN200RG

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)