

# Specifications



## Eaton BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, 11 box size

### Product specifications

<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MOUNTING</b>	Combination
<b>NUMBER OF CIRCUITS</b>	60
<b>NUMBER OF SPACES</b>	30
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>WIRE SIZE</b>	Determined by circuit breaker installed
<b>BOX SIZE</b>	G1
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	3

### General specifications

<b>PRODUCT NAME</b>	Eaton BR convertible loadcenter
<b>CATALOG NUMBER</b>	BR3060NQN200
<b>UPC</b>	786676026369
<b>PRODUCT LENGTH/DEPTH</b>	3.88 in
<b>PRODUCT HEIGHT</b>	34.13 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	34 lb
<b>WARRANTY</b>	10 year
<b>CATALOG NOTES</b>	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

**EATON**

Powering Business Worldwide