



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BR4040B200R 1PH 200A 25KAIC MCB 40/40 Cir. Al Bus Nema 3R *Eaton Corp*

Catalog Number	BR4040B200R
Manufacturer	Eaton Corp
Description	BR Style Load Center, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 5.19 In Overall Width, 29.13 In Overall Height
Weight per unit	37.8 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	200
Cover Type	Interlock cover
max amps	200
max poles/spaces	40
number of spaces	40
Phase	1

Dimensions and Weight

Depth	5.19
Height	29.13
Size	D1r
Width	14.31

Descriptions

Description	1PH 200A 25KAIC MCB 40/40 CIR. AL BUS NEMA 3R
extra long description	ETN BR4040B200R Eaton BR main break

Manufacturer Information

GTIN	00786676446303
UPC	786676446303

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	37.8

Uses, Certifications, and Standards

Mounting	Combination Mount
standard	UL 67,UL 50