



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4040BC200 C/U 40CIR. MB Load Center

Eaton Corp

Catalog Number	BR4040BC200
Manufacturer	Eaton Corp
Description	BR Style 1-Inch Loadcenter, Main Circuit Breaker, No Feed-Thru Lugs, Includes BREQS125 Hold-Down Screw, 200A, Single-Phase, 40-Pole, 40 Circuits, 40 Spaces, 120/240V, #2/0-300 Kcmil Cu/Al At 60°C or 75°C, Nema 1 Enclosure, C2 Box Size
Weight per unit	40.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	59120
Box Size	QUARTZ LIGHTING LENS, GLASS LENS REFRACTOR/LENS TYPE; QF500F QUARTZ FLOODLIGHT FIXTURE TYPE; RAB[R] BRAND
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX58.4200centimetre
interrupt rating	10 kAIC
main circuit breaker	BWH
Number of Circuits	40 W
number of spaces	40 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers
Voltage Rating	120/240 VAC
Wire Size	#2/0-300 kcmil Cu/Al at 60°C or 75°C

Material, Color, and Finish

Bus Material	Copper
Enclosure Material	Metallic

Dimensions and Weight

Size	C2
------	----

Descriptions

Description	C/U 40CIR. MB LOAD CENTER
extra long description	ETN BR4040BC200 BR style 1-inch loa
Long Description	BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, includes BREQS125 hold-down screw, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C, NEMA 1 enclosure, c2 box size
Product Type	BR Style 1-Inch Loadcenter
Special Features	No feed-thru lugs, includes BREQS125 hold-down screw



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00782114867013
Manufacturers Part Number	BR4040BC200
UPC	782114867013

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	Main circuit breaker
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	40

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50