



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR4040L200

UPC:786676447751

Dimensions:

- **Height:** 34.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:34 LB

Notes:Has notch for brhdk125 hold-down kit.

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main lug
- **Amperage Rating:** 200A
- **Box Size:** G1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #1 AWG-300 kcmil Cu/Al

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR4040L200](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.