



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 1P/BR LC, 40 SPACE/50 CIRCUIT CONVERTIBLE 200A BUS N1

**BR4050N200**

**UPC:**786685931449

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.9 IN
- **Width:** 14.3 IN

**Weight:**25 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Factory integrated surge
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 1
- **Number Of Circuits:** 120
- **Number Of Spaces:** 60
- **Phase:** Single-phase
- **Feed Type:** Top/bottom
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - BR4050N200](#)

### Certifications:

- UL E52977

### Product compliance:

- UL67







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 1P/BR LC, 40 SPACE/50 CIRCUIT CONVERTIBLE 200A BUS N1

**BR4050N200**

**UPC:**786685931449

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.9 IN
- **Width:** 14.3 IN

**Weight:**25 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Factory integrated surge
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 1
- **Number Of Circuits:** 120
- **Number Of Spaces:** 60
- **Phase:** Single-phase
- **Feed Type:** Top/bottom
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - BR4050N200](#)

### Certifications:

- UL E52977

### Product compliance:

- UL67



