



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR4080BQN200**

**UPC:**786676026239

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

**Weight:**39 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** QUICK CONNECT NEUTRALS
- **Type:** Main circuit breaker
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 80
- **Number Of Spaces:** 40
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eaton Specification Sheet - BR4080BQN200](#)

**Certifications:** No Data

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BR4080BQN200**

**UPC:**786676026239

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

**Weight:**39 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** QUICK CONNECT NEUTRALS
- **Type:** Main circuit breaker
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 80
- **Number Of Spaces:** 40
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eaton Specification Sheet - BR4080BQN200](#)

**Certifications:** No Data

**Product compliance:** No Data



