

Specifications



Eaton BR816L200RF

Eaton BR main lug loadcenter, Feed-through lug, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 16 Circuits, Twenty-four pole, 8 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR816L200RF
UPC	786676447256
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Feed-through lug
TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	16
NUMBER OF SPACES	8
PHASE	Single-phase
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	B2R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR816L200RF
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton BR816L200RF

Eaton BR main lug loadcenter, Feed-through lug, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 16 Circuits, Twenty-four pole, 8 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR816L200RF
UPC	786676447256
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.8 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Feed-through lug
TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	16
NUMBER OF SPACES	8
PHASE	Single-phase
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	B2R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR816L200RF
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

