

Eaton BR816L200RF

Catalog Number: BR816L200RF

Eaton BR main lug loadcenter, Feed-through lug, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 16 Circuits, Twenty-four pole, 8 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR816L200RF
UPC	Product Length/Depth
786676447256	5.19 in
Product Height	Product Width
18.75 in	14.31 in
Product Weight	Warranty
15.8 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard

Product specifications

Special features

Feed-through lug

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Voltage rating

120/240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

B2R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Specifications and datasheets

[Eaton Specification Sheet - BR816L200RF](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)