

Eaton BRCAF120

Catalog Number: BRCAF120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

General specifications



Photo is representative

| | |
|--|---|
| Product Name | Catalog Number |
| Eaton BR AFCI circuit breaker | BRCAF120 |
| UPC | Product Length/Depth |
| 786685514338 | 6 in |
| Product Height | Product Width |
| 1.25 in | 3.5 in |
| Product Weight | Warranty |
| 0.45 lb | Limited lifetime residential, 1 year commercial |
| Compliances | Certifications |
| Federal Specifications Classification W-C375 | UL 1699 |

Product specifications

Used with

Type BR Loadcenters

Special features

Arc fault

Amperage Rating

20 A

Voltage rating

120 V

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Resources

Catalogs

Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BRCAF120

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia