

Eaton BRHX2110

Catalog Number: BRHX2110

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,110 A,22kAIC,Two-pole,120/240V,BRHX,Non-interchangeable,110,Plug-on,BRHX



Photo is representative

General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton BR thermal magnetic circuit breaker | BRHX2110 |
| | UPC |
| | 786689041663 |
| Product Length/Depth | Product Height |
| 2.6 in | 2 in |
| Product Width | Product Weight |
| 1.9 in | 0.75 lb |
| Warranty | Certifications |
| 1 year | Contact Manufacturer |

Product specifications

Type

Quicklag Type BRHX circuit breaker

Amperage Rating

110

Voltage rating

120/240 V

Trip Type

Non-interchangeable

Circuit breaker type

BR

Mounting Method

Plug-on

Interrupt rating

22 kAIC

Main circuit breaker

BR

Connection

Plug-on

Number of poles

Two-pole

Trip rating

110 A

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRHX2110](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)