

Specifications



Photo is representative



Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 125, Plug-on, BRHX

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton BR thermal magnetic circuit breaker |
| CATALOG NUMBER | BRHX2125 |
| UPC | 786689041670 |
| PRODUCT LENGTH/DEPTH | 3.1 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.2 in |
| PRODUCT WEIGHT | 0.9 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | Contact Manufacturer |



Powering Business Worldwide

| Product specifications | |
|------------------------|------------------------------------|
| TYPE | Quicklag Type BRHX circuit breaker |
| AMPERAGE RATING | 125 |
| VOLTAGE RATING | 120/240 V |
| TRIP TYPE | Non-interchangeable |
| CIRCUIT BREAKER TYPE | BR |
| MOUNTING METHOD | Plug-on |
| INTERRUPT RATING | 22 kAIC |
| MAIN CIRCUIT BREAKER | BR |
| CONNECTION | Plug-on |
| NUMBER OF POLES | Two-pole |
| TRIP RATING | 125 |

| Resources | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BRHX2125 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 125, Plug-on, BRHX

General specifications

| | |
|----------------------|---|
| PRODUCT NAME | Eaton BR thermal magnetic circuit breaker |
| CATALOG NUMBER | BRHX2125 |
| UPC | 786689041670 |
| PRODUCT LENGTH/DEPTH | 3.1 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.2 in |
| PRODUCT WEIGHT | 0.9 lb |
| WARRANTY | 1 year |
| CERTIFICATIONS | Contact Manufacturer |



Powering Business Worldwide

| Product specifications | |
|------------------------|------------------------------------|
| TYPE | Quicklag Type BRHX circuit breaker |
| AMPERAGE RATING | 125 |
| VOLTAGE RATING | 120/240 V |
| TRIP TYPE | Non-interchangeable |
| CIRCUIT BREAKER TYPE | BR |
| MOUNTING METHOD | Plug-on |
| INTERRUPT RATING | 22 kAIC |
| MAIN CIRCUIT BREAKER | BR |
| CONNECTION | Plug-on |
| NUMBER OF POLES | Two-pole |
| TRIP RATING | 125 |

| Resources | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BRHX2125 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| DATE: |



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

