

Eaton BRP08E200RF

Catalog Number: BRP08E200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V

General specifications



Photo is representative

Product Name

Eaton BR convertible loadcenter

Catalog Number

BRP08E200RF

UPC

786689059804

Product Length/Depth

5.19 in

Product Height

5.7 in

Product Width

14.31 in

Product Weight

18 lb

Warranty

10 year

Certifications

UL 67

UL 50

Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

defaultTaxonomyAttributeLabel

Special features

Feed-through lug

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#1 AWG-300 kcmil

Box size

X2

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP08E200RF](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP08E200RF

Catalog Number: BRP08E200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V

General specifications



Photo is representative

Product Name

Eaton BR convertible loadcenter

Catalog Number

BRP08E200RF

UPC

786689059804

Product Length/Depth

5.19 in

Product Height

5.7 in

Product Width

14.31 in

Product Weight

18 lb

Warranty

10 year

Certifications

UL 67

UL 50

Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Feed-through lug

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#1 AWG-300 kcmil

Box size

X2

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP08E200RF](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia