

# Eaton BRP10B100

Catalog Number: BRP10B100

Plug-on neutral main circuit breaker loadcenter, 100A, X0, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR, 20 circuits, Single pole, 10 spaces, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG Cu/Al, 25, Kilo Ampere, 10 kAIC, Gray, Combinati



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP10B100
<b>UPC</b>	<b>Product Length/Depth</b>
786689054939	16.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
16.5 lb	10 year

## Certifications

UL 67  
UL 50

## defaultTaxonomyAttributeLabel

### Special features

Main circuit breaker

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

100 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

20

### Number Of Poles

Single-pole

### Number of spaces

10

### Phase

Single-phase

### Wire size

#6-1/0 AWG Cu/Al

### Bus Rating

25 kA

### Enclosure color

Gray

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X0

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP10B100

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

10 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP10B100

Catalog Number: BRP10B100

Plug-on neutral main circuit breaker loadcenter, 100A, X0, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR, 20 circuits, Single pole, 10 spaces, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG Cu/Al, 25, Kilo Ampere, 10 kAIC, Gray, Combinati



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP10B100
<b>UPC</b>	<b>Product Length/Depth</b>
786689054939	16.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
16.5 lb	10 year

## Certifications

UL 67  
UL 50

## defaultTaxonomyAttributeLabel

### Special features

Main circuit breaker

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

100 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

20

### Number Of Poles

Single-pole

### Number of spaces

10

### Phase

Single-phase

### Wire size

#6-1/0 AWG Cu/Al

### Bus Rating

25 kA

### Enclosure color

Gray

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X0

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP10B100

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

10 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)