

Eaton BRP12L125

Catalog Number: BRP12L125

Eaton Eaton BR main lug loadcenter, Indoor, Main lug only, 125 A, X0, Aluminum, NEMA 1, Metallic, 10kAIC, Surface, flush, 24 Circuits, Twenty-four pole, 12 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V, #6-2/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP12L125
UPC	Product Length/Depth
786689052959	16.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
16.1 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Mounting

Surface, flush

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

X0

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12L125](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)