

Eaton BRP12L125G

Catalog Number: BRP12L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X0, Aluminum, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, 24 Circuits, Twenty-four pole, 12 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP12L125G
UPC	Product Length/Depth
786689053000	16.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
16.1 lb	10 year

Certifications

UL 67
UL 50

defaultTaxonomyAttributeLabel

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2125

Mounting

Surface, flush

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-2/0 AWG Cu/Al

Box size

X0

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12L125G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)