

Eaton BRP16N200

Catalog Number: BRP16N200

Eaton BR convertible loadcenter, Convertible, 200 A, X4, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 32 Circuits, Single-pole, 16 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP16N200 |
| UPC | Product Length/Depth |
| 786689053147 | 27 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 26.8 lb | 10 year |
| Certifications | |
| UL 50 | |
| UL 67 | |

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP16N200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP16N200

Catalog Number: BRP16N200

Eaton BR convertible loadcenter, Convertible, 200 A, X4, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 32 Circuits, Single-pole, 16 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP16N200 |
| UPC | Product Length/Depth |
| 786689053147 | 27 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 26.8 lb | 10 year |
| Certifications | |
| UL 50 | |
| UL 67 | |

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP16N200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)