

# Eaton BRP16N200

Catalog Number: BRP16N200

Eaton BR convertible loadcenter, Convertible, 200 A, X4, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 32 Circuits, Single-pole, 16 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BRP16N200
<b>UPC</b>	<b>Product Length/Depth</b>
786689053147	27 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26.8 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## Product specifications

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Mounting

Combination

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X4

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP16N200](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)