

Eaton BRP20B150

Catalog Number: BRP20B150

Plug-on neutral main circuit breaker loadcenter, 150A, X4, Aluminum, Cover included, NEMA 1, Metallic, 25kAIC, CSR2150, 40 circuits, Single pole, 20 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP20B150
UPC	Product Length/Depth
786689053178	27 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
26.2 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2150

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20B150

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)