

Specifications



Photo is representative



Eaton BRP20N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP20N125R
UPC	786689059316
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	18 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications	
TYPE	Convertible
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Combination
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP20N125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton BRP20N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP20N125R
UPC	786689059316
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	18 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications	
TYPE	Convertible
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
MOUNTING	Combination
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X4
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	3

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP20N125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

