

Specifications



Eaton BRP20N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP20N200G
UPC	786689053307
PRODUCT LENGTH/DEPTH	29.12 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Ground bar
TYPE	Convertible
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
MOUNTING	Combination
NUMBER OF CIRCUITS	40
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	20
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X5
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NUMBER OF WIRES	Two hots, neutral and ground

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP20N200G
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

