

# Eaton BRP30B200RV25

Catalog Number: BRP30B200RV25

BR plug-on neutral loadcenter value pack, 200A, main breaker, 30 spaces, NEMA 3R w/ (2) BR120 & (1) BR230



## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B200RV25
UPC	Product Length/Depth
786689058432	34.12 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
26 lb	10 year
Certifications	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Special features

Value pack

### Type

Main circuit breaker

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

60

### Number Of Poles

Single-pole

### Number of spaces

30

### Phase

Single-phase

### Wire size

#4-1/0 AWG Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X6

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30B200RV25](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

25 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)