

# Specifications



## Eaton BRP30BC100

Eaton BR main breaker loadcenter, 100A, X5, Copper, Cover included, NEMA 1, Metallic, 10kAIC, BR2100, 60 circuits, Single pole, 30 spaces, Two hots, a neutral, and a ground, Single-phase, Combination, Type BR 1-inch breakers, 120/240V

### Product specifications

TYPE	Plug neut circu break load
AMPERAGE RATING	100
BUS MATERIAL	Cop
COVER	Cove inclu
MAIN CIRCUIT BREAKER	BR2
NUMBER OF CIRCUITS	60
NUMBER OF POLES	Sing
NUMBER OF SPACES	30
PHASE	Sing
MOUNTING	Com
USED WITH	Type inch break
VOLTAGE RATING	120/
BOX SIZE	X5
ENCLOSURE	NEM
ENCLOSURE MATERIAL	Meta
INTERRUPT RATING	10 k
NUMBER OF WIRES	Two neut grou

### General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP30BC100
UPC	786689052829
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	27.5 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide