

Specifications

Eaton BRP40N200

Eaton BR convertible loadcenter,Ground bar, includes BREQS125 hold-down screw,200 A,X8,Aluminum,Cover included,NEMA 1,Metallic,25 kAIC,CSR,Combination,80 Circuits,Single-pole,40 Spaces,Single-phase,Type BR 1-inch breakers,120/240 V

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BRP40N200
UPC	786689044077
PRODUCT LENGTH/DEPTH	39 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.13 in
PRODUCT WEIGHT	27 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
PRODUCT TYPE	Convertible loadcenter

Product specifications

SPECIAL FEATURES	Ground bar, includes BREQS125 hold-down screw
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
MOUNTING	Combination
NUMBER OF CIRCUITS	80
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	40
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X8
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP40N200
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

