

Eaton BRP40N200RG

Catalog Number: BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200RG
UPC	Product Length/Depth
786689059064	3.88 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year

Certifications

UL 50
UL 67

Product specifications

Special features

Ground bar

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Specifications and datasheets

Eaton Specification Sheet - BRP40N200RG

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)