

Specifications



Photo is representative



Eaton BRP60B200R

Plug-on neutral main circuit breaker loadcenter, 200A, X10, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 120 circuits, Single pole, 60 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP60B200R
UPC	786689059088
PRODUCT LENGTH/DEPTH	48.75 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	35 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

TYPE	Plug-on neutral main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	120
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	60
PHASE	Single-phase
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X10
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3
NEMA RATING	NEMA 3R

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP60B200R](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton BRP60B200R

Plug-on neutral main circuit breaker loadcenter, 200A, X10, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 120 circuits, Single pole, 60 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BRP60B200R
UPC	786689059088
PRODUCT LENGTH/DEPTH	48.75 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	35 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50



Powering Business Worldwide

Product specifications

TYPE	Plug-on neutral main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	120
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	60
PHASE	Single-phase
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	X10
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3
NEMA RATING	NEMA 3R

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRP60B200R](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

