

Eaton BRP60E200

Catalog Number: BRP60E200

Eaton BR convertible loadcenter, Convertible, lugs installed, 200 A, X10, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 120 Circuits, Single-pole, 60 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP60E200
UPC	Product Length/Depth
786689055066	48 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
41 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Convertible, lugs installed

Type

Convertible, lugs installed

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

120

Number Of Poles

Single-pole

Number of spaces

60

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#6-1/0 AWG Cu/Al

Box size

X10

Enclosure

NEMA 1

Enclosure material

Metallic

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP60E200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP60E200

Catalog Number: BRP60E200

Eaton BR convertible loadcenter, Convertible, lugs installed, 200 A, X10, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 120 Circuits, Single-pole, 60 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP60E200
UPC	Product Length/Depth
786689055066	48 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
41 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Convertible, lugs installed

Type

Convertible, lugs installed

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

120

Number Of Poles

Single-pole

Number of spaces

60

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#6-1/0 AWG Cu/Al

Box size

X10

Enclosure

NEMA 1

Enclosure material

Metallic

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP60E200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)