

# Eaton BRP60E200

Catalog Number: BRP60E200

Eaton BR convertible loadcenter, Convertible, lugs installed, 200 A, X10, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 120 Circuits, Single-pole, 60 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240 V



## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP60E200
UPC	Product Length/Depth
786689055066	48 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
41 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

Convertible, lugs installed

### Type

Convertible, lugs installed

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Mounting

Combination

### Number of circuits

120

### Number Of Poles

Single-pole

### Number of spaces

60

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

#6-1/0 AWG Cu/Al

### Box size

X10

### Enclosure

NEMA 1

### Enclosure material

Metallic

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP60E200](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)