



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRPSURGE10 Type BR 2 Pole Pon Surge Arrester

Eaton Corp

Catalog Number	BRPSURGE10
Manufacturer	Eaton Corp
Description	Eaton Type BR Circuit Breaker Surge Protective Device, Two Pole, Plug-On Neutral Surge Protective Device, 10 Ka
Weight per unit	0.5400 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	3.6000 IN X 3.5000 IN X 2.4000 IN
------------	-----------------------------------

Dimensions and Weight

Depth	3.6
Height	2.4
Width	3.5

Descriptions

Description	TYPE BR 2 POLE PON SURGE ARRESTER
extra long description	ETN BRPSURGE10 TYPE BR 2 POLE PON S
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	EATON TYPE BR CIRCUIT BREAKER SURGE PROTECTIVE DEVICE, TWO POLE, PLUG-ON NEUTRAL SURGE PROTECTIVE DEVICE, 10 KA
Product Type	Type BR 2 Pole Pon Surge Arrester

Manufacturer Information

Brand	Eaton Corp
Manufacturers Part Number	BRPSURGE10

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Plug on module surge protection device

Packaging

Carton	1
Weight Per each	0.54



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

OtherOther

standard

UL 1449,cUL Certified