



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSN10L Nylon-Ins Butt Splice

Panduit Corporation

Catalog Number	BSN10L
Manufacturer	Panduit Corporation
Description	Panduit BSN10-L Nylon Insulated Butt Splice
Weight per unit	0.3250 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	12 - 10
------	---------

Descriptions

Description	NYLON-INS BUTT SPLICE
extra long description	PAN BSN10-L Pan-Term® BSN10-L Butt
Long Description	Panduit BSN10-L Nylon Insulated Butt Splice
Product Type	Pan-Term® BSN10-L Butt Splice, Yellow, Nylon, 10-12 Awg, PK5

Manufacturer Information

Brand	PANDUIT
GTIN	00074983830046
Manufacturers Part Number	BSN10-L
UPC	074983830046

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Butt Splice

Packaging

Carton	50
Package	250
Weight Per each	0.325



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting	9/32
standard	BSN10-L
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)