



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSV10Q Highland Vinyl Ins Butt Connector, 12-10awg *Minnesota Mining (3M)*

Catalog Number	BSV10Q
Manufacturer	Minnesota Mining (3M)
Description	Butt Splice, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Copper Conductor Material, 600 V (Building Wiring);1000 V (Signs/Fixture), -40 °F Operating Temperature, +221 °F Operating Temperature, 1.02 In Overall Length, Butt Splice Terminal, 600 V, 0.15 LB
Weight per unit	0.0148 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	HIGHLAND VINYL INS BUTT CONNECTER, 12-10AWG
extra long description	3M 7000133654 3M™ Highland™ Vinyl I

Manufacturer Information

Brand	Scotchlok
GTIN	00051128599969
Manufacturers Part Number	7000133654
UPC	051128599969

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Butt Splice

Packaging

Carton	1
Package	10
Weight Per each	0.0148

Uses, Certifications, and Standards

standard	UL and CSA
----------	------------