



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSV10Q Highland Vinyl Ins Butt Connector, 12-10awg *Minnesota Mining (3M)*

Catalog Number	BSV10Q
Manufacturer	Minnesota Mining (3M)
Description	Butt Splice, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Copper Conductor Material, 600 V (Building Wiring);1000 V (Signs/Fixture), -40 °F Operating Temperature, +221 °F Operating Temperature, 1.02 In Overall Length, Butt Splice Terminal, 600 V, 0.15 LB
Weight per unit	0.0148 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	HIGHLAND VINYL INS BUTT CONNECTER, 12-10AWG
extra long description	3M 7000133654 3M™ Highland™ Vinyl I

Manufacturer Information

Brand	Scotchlok
GTIN	00051128599969
Manufacturers Part Number	7000133654
UPC	051128599969

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Butt Splice

Packaging

Carton	10
Weight Per each	0.0148

Uses, Certifications, and Standards

standard	UL and CSA
----------	------------