



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BSV10XQ 12-10 Vinyl Ins Butt Splice Ylw *Panduit Corporation*

Catalog Number	BSV10XQ
Manufacturer	Panduit Corporation
Description	Panduit BSV10X-Q Vinyl Insulated Butt Splice
Weight per unit	0.2250 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Expanded
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600

Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

Dimensions and Weight

Size	12 - 10
------	---------

Descriptions

Description	12-10 VINYL INS BUTT SPLICE YLW
extra long description	PAN BSV10X-Q Pan-Term® BSV10X-Q But
Long Description	Panduit BSV10X-Q Vinyl Insulated Butt Splice
Product Type	Pan-Term® BSV10X-Q Butt Splice, Yellow, Vinyl, 10-12 Awg, PK

Manufacturer Information

Brand	PANDUIT
GTIN	00074983521616
Manufacturers Part Number	BSV10X-Q
UPC	074983521616

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Butt Splice

Availability

minimum qty	25
-------------	----

Packaging

Carton	25
Package	250
Weight Per each	0.225



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting	5/16
standard	BSV10X-Q
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)