



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT3SC0 Nylon Cable Tie *Panduit Corporation*

Catalog Number	BT3SC0
Manufacturer	Panduit Corporation
Description	The BT3S-C0 Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Standard Cross Section, 12.0" (305MM) Length. Appropriate For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6 With High Resistance to Ultraviolet Light, Are Black In Color and Come In Packages Of 100.
Weight per unit	0.0006 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	12
Thickness	0.05

Descriptions

Description	NYLON CABLE TIE
extra long description	PAN BT3S-C0 Dome-Top® BT3S-C0 Barb
Long Description	The BT3S-C0 Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Standard cross section, 12.0" (305mm) length. Appropriate for Indoor/Outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 100.
Product Type	Dome-Top® BT3S-C0 Barb Tie, Black, Uv PA6.6, 12"L, 50LB, PK1
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983412075
Manufacturers Part Number	BT3SC0
UPC	074983412075



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Cable Tie

Packaging

Carton	100
Package	1000
Weight Per each	0.0006

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, OPL-AS23190, CSA Certified, RoHS Compliant
----------	---