ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT7LHL0 24.4" 120LB BLK Dome-Top Barb CBL Tie

Panduit Corporation

Catalog Number	BT7LHL0
Manufacturer	Panduit Corporation
Description	The Dome-Top® BT7LH-L0 Cable Tie Provides High-Strength Bundling For Indoor/Outdoor Routing and Organization Requiring Uv and Weather Resistance. Light-Heavy Style, 24.4 In (620MM) Long With 120 LB (534 N) Minimum Loop Tensile Strength and A 0.188–7 In (4.8–177.8MM) Bundle Diameter Range. It Is Black Nylon 6.6 (Uv-Resistant, Weather-Resistant). Operating Range -76 to 185°F (-60 to 85°C). Use With GTH-E, GS4H-E, GS4EH-E, PTH, STH2, and ST3EH Tools.
Weight per unit	1.1 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	120

Dimensions and Weight

Length	24.4
Thickness	0.07

Descriptions

Description	24.4" 120LB BLK DOME-TOP BARB CBL TIE
extra long description	PAN BT7LH-L0 Cable Tie, Black UV PA
Long Description	The Dome-Top® BT7LH-L0 cable tie provides high-strength bundling for indoor/outdoor routing and organization requiring UV and weather resistance. Light-heavy style, 24.4 in (620mm) long with 120 lb (534 N) minimum loop tensile strength and a 0.188–7 in (4.8–177.8mm) bundle diameter range. It is black Nylon 6.6 (UV-Resistant, Weather-Resistant). Operating range -76 to 185°F (-60 to 85°C). Use with GTH-E, GS4H-E, GS4EH-E, PTH, STH2, and ST3EH tools.
Product Type	Cable Tie, Black Uv PA6.6, 24.4"L (620MM), 120LB, PK50
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983412860
Manufacturers Part Number	BT7LH-L0
UPC	074983412860

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Availability

minimum qty	50

Packaging

Carton	50
Package	500
Weight Per each	1.05

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275 (File 31212), Cert 05968/C0, BV File ACE 14/601/01 Product Code: 2535H, 89/60111 (E3), 11130200, QPL-AS23190, RoHS Compliant