



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BU58S SPRG Unv BM Clamp, 5/16-1/2FLNG, 1/4"-20X3/8 *Cooper B-Line/Cable Tray*

Catalog Number	BU58S
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Beam Fasteners, Beams, Flange, 1" Height, 1" Length, 1" Width, 0.065LBS, 20 X 0.38" Ked Stud, Universal Beam Fasteners, .31" Min Mount Size, .5" Max Mount Size
Weight per unit	0.0007 (lbs/each)
Product Category	Anchors & Fasteners

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
Material	Low Carbon Steel

Material, Color, and Finish

Finish	Zinc Phosphate
--------	----------------

Dimensions and Weight

Size	4-1/8 In (OD), 4 In (Copper Tube)
------	-----------------------------------

Descriptions

Construction	TWO PIECE
Description	SPRG UNV BM CLAMP,5/16-1/2FLNG,1/4"-20X3/8
extra long description	B-LINE BU-5-8-S UNIVERSAL BM FS, 5/
Features	Eaton offers a wide variety of beam fasteners designed to attach to I-beams to support or suspend equipment.
Long Description	Eaton B-Line series beam fasteners, Beams, Flange, 1" Height, 1" Length, 1" Width, 0.065lbs, 20 x 0.38" ked stud, Universal beam fasteners, .31" Min mount size, .5" Max mount size
Product Type	Universal BM FS, 5/16" to 1/2" Flange, Staked Stud
Special Features	Includes Cushion, Clamp, Screw and Nut, Dielectric Strength 400 Volts/Mil, 4.73 In Width X 5.55 In Height

Manufacturer Information

Brand	Eaton
GTIN	00781011196202
Manufacturers Part Number	BU-5-8-S
UPC	781011196202

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Beam fasteners



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.0007

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	UL/cUL Listed
Temperature Rating	-40 To 300 Deg F