



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C.2 #2AWG Cu Comp Splice

*Nsi Industries*

Catalog Number	C.2
Manufacturer	Nsi Industries
Description	Long Barrel TINNEDCOPPERSPLICE2 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	3.9 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Warranty	1 YEAR
----------	--------

### Descriptions

Description	#2AWG CU COMP SPLICE
extra long description	NSI C-2 Easy Twist Closed End Conn
Features	Long Barrel TinnedCopperSplice2 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Long Barrel TinnedCopperSplice2 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Easy Twist Closed End Conn 12-10 50 Pack

### Manufacturer Information

Brand	NSi
GTIN	00662381037534
UPC	662381037534

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
----------------------	-----------------------------------

### Packaging

Carton	1
Package	50
Weight Per each	3.9