

# Eaton C0050E2A

Catalog Number: C0050E2A

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 50 va



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Type MTE industrial control transformer	C0050E2A
	<b>UPC</b>
	786680422522
<b>Product Length/Depth</b>	<b>Product Height</b>
3.61 in	3.26 in
<b>Product Width</b>	<b>Product Weight</b>
3 in	2.7 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	cUL Certified
	UL Listed
	CSA Certified

## Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

## Physical Attributes

### Coil material

Copper windings

### Design

MTE

### Tap size

None

## Performance Ratings

### Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

### Temperature rating

55°C

### Volt ampere rating

50 VA

### Secondary voltage

120/115/110 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - C0050E2A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)