



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C0050E2AXXFB 50VA Mte Industrial Control Transformer W/Primary

Eaton Corp

Catalog Number	C0050E2AXXFB
Manufacturer	Eaton Corp
Description	Eaton, Type Mte, Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, 50 Va, Cu Magnet Wire, SV: 120/115/110V, 55°C
Weight per unit	6.0 (lbs/each)
Product Category	Core & Coil Industrial Control

### Features

dimensions	5.0000 IN X 5.0000 IN X 4.0000 IN
kva rating	50 VA
Primary Voltage	230 x 460 V240 x 480 V220 x 440 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

### Descriptions

Description	50VA MTE INDUSTRIAL CONTROL TRANSFORMER W/PRIMARY
extra long description	ETN C0050E2AXXFB 50VA MTE CPT w/PRI
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton, type MTE, industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, 50 va, cu magnet wire, sv: 120/115/110v, 55°C
Product Type	50VA Mte CPT W/Prim Fuseblock

### Manufacturer Information

Brand	Eaton
GTIN	00786680031434
Manufacturers Part Number	C0050E2AXXFB
UPC	786680031434

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	6

## Uses, Certifications, and Standards

Application	Other
standard	UL Listed,CSA Certified,cUL Certified,RoHS Compliant
Temperature Rating	55°C