



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0050E2AXXFB 50VA Mte Industrial Control Transformer W/Primary

Eaton Corp

Catalog Number	C0050E2AXXFB
Manufacturer	Eaton Corp
Description	Eaton, Type Mte, Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, Taps: None, 50 Va, Cu Magnet Wire, SV: 120/115/110V, 55°C
Weight per unit	6.0 (lbs/each)
Product Category	Core & Coil Industrial Control

Features

dimensions	5.0000 IN X 5.0000 IN X 4.0000 IN
kva rating	50 VA
Primary Voltage	230 x 460 V240 x 480 V220 x 440 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	50VA MTE INDUSTRIAL CONTROL TRANSFORMER W/PRIMARY
extra long description	ETN C0050E2AXXFB 50VA MTE CPT w/PRI
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton, type MTE, industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, 50 va, cu magnet wire, sv: 120/115/110v, 55°C
Product Type	50VA Mte CPT W/Prim Fuseblock

Manufacturer Information

Brand	Eaton
GTIN	00786680031434
Manufacturers Part Number	C0050E2AXXFB
UPC	786680031434

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	6

Uses, Certifications, and Standards

Application	Other
standard	UL Listed,CSA Certified,cUL Certified,RoHS Compliant
Temperature Rating	55°C