



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0250E2AFB

UPC:786680420900

Dimensions:

- **Height:** 5.197 IN
- **Length:** 4.37 IN
- **Width:** 4.488 IN

Weight:10.2 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 240 X 480V, 230 X 460V, 220 X 440V
- **Secondary Voltage:** 120/115/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 250 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [MTE Control Transformer 250 VA Series 2 -](#)



C0250E2AFB

- Eaton Specification Sheet - C0250E2AFB

Certifications:

- cUL Certified
- CSA Certified
- UL Listed

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0250E2AFB

UPC:786680420900

Dimensions:

- **Height:** 5.197 IN
- **Length:** 4.37 IN
- **Width:** 4.488 IN

Weight:10.2 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Modification 1:** Factory-mounted 2-pole primary fuse block for rejection type fuses
- **Primary Voltage:** 240 X 480V, 230 X 460V, 220 X 440V
- **Secondary Voltage:** 120/115/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 250 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [MTE Control Transformer 250 VA Series 2 -](#)



C0250E2AFB

- Eaton Specification Sheet - C0250E2AFB

Certifications:

- cUL Certified
- CSA Certified
- UL Listed

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.