

Eaton C0250E2AFB

Catalog Number: C0250E2AFB

Eaton Type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 250 va, taps: none

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0250E2AFB
	UPC
	786680420900
Product Length/Depth	Product Height
4.18 in	5.29 in
Product Width	Product Weight
4.5 in	9.3 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	cUL Certified
	CSA Certified
	UL Listed

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

220 x 440 V, 230 x 460 V, 240 x 480 V

Temperature rating

55°C

Volt ampere rating

250 VA

Secondary voltage

120/115/110 V

Miscellaneous

Modification 1

Factory-mounted two-pole primary fuse block for non-rejection type fuses

Special features

Primary fuse block

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0250E2AFB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)