



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C1.5BL6 1-1/2 Black CVR P/FT *Panduit Corporation*

Catalog Number	C1.5BL6
Manufacturer	Panduit Corporation
Description	The C1.5BL6 PVC Flush Wiring Duct Cover Features A Non-Slip, Liner to Prevent Cover Slide. Designed With The User In Mind, The Cover Is Easy to Install and Remove. The General-Purpose Lead-Free PVC Material Is Suitable For Use In Indoor Applications. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up to 122°F (50°C). 0.35" X 1.75" (8.9 MM X 44.5 MM) and 6' (1.83 M) Long. Color Black.
Weight per unit	0.5300 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Snap-on
media	Yes

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	NA
Width	1.75

Descriptions

Description	1-1/2 BLACK CVR P/FT
extra long description	PAN C1.5BL6 Panduct® C1.5BL6 Flush
Long Description	The C1.5BL6 PVC Flush Wiring Duct Cover features a non-slip, liner to prevent cover slide. Designed with the user in mind, the cover is easy to install and remove. The general-purpose lead-free PVC material is suitable for use in indoor applications. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). 0.35" x 1.75" (8.9 mm x 44.5 mm) and 6' (1.83 m) long. Color Black.
Product Type	Panduct® C1.5BL6 Flush Duct Cover

Manufacturer Information

Brand	PANDUIT
GTIN	00074983230594
Manufacturers Part Number	C1.5BL6
UPC	074983230594



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description WIRE DUCT AND COVERS

Type Flushed Duct Cover

Packaging

Carton 120

Weight Per each 0.53

Uses, Certifications, and Standards

Application Cover for Wiring Duct

standard CE Compliant;CSA Certified;Flammability Ratings: UL94 V-0;RoHS
Compliant;UL Recognized