



C11HD4/ODB, Cast Bronze Ground Clamp for Water Pipe, Rebar, Ground Rod to Tap Conductor

By Burndy
Catalog # C11HD4/ODB



Cast Bronze Ground Clamps, Water Pipe/Rebar/Ground Rod - Ground, Water Pipe- 1/2"-1" (13 -25) (Run), Rebar- #4 -#6 (Run) Ground Rod -3/8"-1" (Run), Water Pipe- 1/2 " - 1 "(13 -25) (Run), Rebar #4-#6 (Run), Ground Rod -3/8" - 1" (Run), Ground-#8 - 4/0 (Tap).

General

Application	For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications
Catalog Number	C11HD4/ODB
EU RoHS Indicator	Yes
Installation Torque	50 LBS/in
Recommended in-lb	
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel
Plating Type	N
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810347751
UPC 12 Digit	7818103477511

Dimensions

Dimension - Height fraction	2.888888888888889 in
Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.65 in
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	8 AWG - 4/0 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 -1
Conductor - Rebar Size	4 ;5 ;6
Conductor - Rebar Size Range	4 -6
Conductor - Rod Size	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in
Conductor - Rod Size Range	3/8 in-1 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - C11HD40DB_MODEL-IGES](#)

[3D Models - C11HD40DB_MODEL-PDF](#)

[3D Models - C11HD40DB_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_C11HD4_LineArt](#)

[Sales Drawings - SC210668-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-C11HD40DB-SPEC-EN | REV 6/2024