



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DND330A Open N-R 3P 30A DP Cont SCR/PP W/QC Term 120VAC CO *Eaton Corp*

Catalog Number	C25DND330A
Manufacturer	Eaton Corp
Description	Definite Purpose Control - Contactor, 3 Poles, 30 A, 110 to 120 V Ac, 40 A Resistive Load, 1/3 Phases, 5 HP (Single Phase);10 HP (Three Phase);3.7 KW (Single Phase);7.5 KW (Three Phase) Motor Power, 15 to 50 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.35 In Overall Length, 2.40 In Overall Width, 1.19 LB
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 2.5000 IN
Enclosure Type	Open with metal mounting plate
induct amp/res amp rating	30/40
Voltage Rating	120

Dimensions and Weight

Depth	3.35
Height	2.5
Width	2.4

Descriptions

Description	OPEN N-R 3P 30A DP CONT SCR/PP W/QC TERM 120VAC CO
extra long description	ETN C25DND330A OP N-R 3P 30ADPCNT S

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300587
UPC	782116300587

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Package	20
Weight Per each	1.19

Uses, Certifications, and Standards

standard	UL Recognized,CSA Certified,RoHS Compliant
----------	--