



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DNF240B Open N-R 2P 40A DP Cont Box Lugs W/QC Term 240vac *Eaton Corp*

Catalog Number	C25DNF240B
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 208-240 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, 2P, 50A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Coil Voltage	50/60 Hz
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

Descriptions

Description	OPEN N-R 2P 40A DP CONT BOX LUGS W/QC TERM 240VAC
extra long description	ETN C25DNF240B OP N-R 2P 40ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick,40A,208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, 2P, 50A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing
Product Type	Op N-R 2P 40ADPCNT BXLGS W/Qc240ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300402
Manufacturers Part Number	C25DNF240B
UPC	782116300402

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 1.19

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard UL Recognized, CSA Certified, RoHS Compliant