

# Specifications



Photo is representative



## Eaton C25DNF330A

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 110/120 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

<b>PRODUCT NAME</b>	Eaton definite purpose contactor
<b>CATALOG NUMBER</b>	C25DNF330A
<b>UPC</b>	782116300594
<b>PRODUCT LENGTH/DEPTH</b>	3.35 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	2.4 in
<b>PRODUCT WEIGHT</b>	1.05 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
TYPE	Non-reversing
COIL	208-240 Vac, 50/60 Hz
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactactor
RESISTIVE LOAD	40 A
TERMINALS	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
CONNECTION	Quick

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - C25DNF330A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

