

Eaton C25DNF330B

Catalog Number: C25DNF330B

Eaton definite purpose contactor, Quick, 30A, 110V/50 Hz, 120V/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF330B
UPC	Product Length/Depth
782116311347	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
1.3 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)

Product specifications

Amperage Rating

30A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (side-by-side)

Coil

208-240 Vac, 50/60 Hz

Coil voltage

440-480 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Specifications and datasheets

Eaton Specification Sheet - C25DNF330B

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C25DNF330B

Catalog Number: C25DNF330B

Eaton definite purpose contactor, Quick, 30A, 110V/50 Hz, 120V/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF330B
UPC	Product Length/Depth
782116311347	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
1.3 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)

Product specifications

Amperage Rating

30A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (side-by-side)

Coil

208-240 Vac, 50/60 Hz

Coil voltage

440-480 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Specifications and datasheets

Eaton Specification Sheet - C25DNF330B

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)